

## KLIPPEL BFS System - Package Examples

Examples only. Please check components for your application with the specifications or send a request to KLIPPEL.

Effective from April 04, 2023. Currency: EURO. All prices net, EXW (tax, duty, transportation, support extra).

Klippel GmbH, Germany, Tel.: +49-351-501 939 0, Fax.: +49-351-501 939 10, E-Mail: [info@klippel.de](mailto:info@klippel.de), Web: [www.klippel.de](http://www.klippel.de)

<b>B-Field Scanner - complete set including all required Klippel components</b>			
Hardware <sup>1</sup>	Klippel Analyzer 3 (LSX)	7.560	€
Module	TRF Standard - Transfer Function Measurement Standard	1.140	€
	BFS - B-Field Scanner Software	3.740	€
SCN Hardware	3D Scanner incl. Motor Control (hardware only)	23.300	€
Accessory	BFS-Sensor	750	€
	Reference Magnet for B-Field Scanner <sup>4</sup>	920	€
	<b>total:</b>	<b>37.410</b>	<b>€</b>

<b>B-Field Scanner - add-on to an existing Klippel RnD System with Scanning Vibrometer</b>			
Module	BFS - B-Field Scanner Software	3.740	€
Accessory	BFS-Sensor	750	€
	Reference Magnet for B-Field Scanner <sup>4</sup>	920	€
	<b>total:</b>	<b>5.410</b>	<b>€</b>

<b>B-Field Scanner - add-on to an existing Klippel RnD System without Scanning Vibrometer</b>			
SCN Hardware	3D Scanner incl. Motor Control (hardware only)	23.300	€
Module	BFS - B-Field Scanner Software <sup>2</sup>	3.740	€
Accessory	BFS-Sensor	750	€
	Reference Magnet for B-Field Scanner <sup>4</sup>	920	€
	<b>total:</b>	<b>28.710</b>	<b>€</b>

<b>B-Field hand-held Probe - add-on to an existing Klippel RnD System<sup>3</sup></b>			
Accessory	BFS-Sensor	750	€
	Reference Magnet for B-Field Scanner <sup>4</sup>	920	€
	<b>total:</b>	<b>1.670</b>	<b>€</b>

<b>B-Field Scanner - hand-held Gauss meter</b>			
Hardware <sup>1</sup>	Klippel Analyzer 3 (LSX)	7.560	€
Accessory	BFS-Sensor	750	€
<b>total:</b>		<b>8.310</b>	<b>€</b>

<sup>1</sup>also required: Computer and Amplifier or Klippel Analyzer 3 with Amp Card: 8.560 €

<sup>2</sup>also required: TRF required

<sup>3</sup>only KA3 required

<sup>4</sup>Any speaker magnet with known magnetic flux density could be used alternatively as reference magnet.